

Sterile goods transport cart for 6 STU

Product code	Type
7504647	STW/M 6StE 985/751/1471

FUNCTIONAL DESCRIPTION

Sterile supply transport trolley for transport and storage of standardised sterile supplies containers and baskets. 160 mm stainless steel castors as standard.

- Closed design with hinged doors provides secure storage and protects contents from external influences
- Transport latch with sealing ensures reliable locking and prevents unauthorised access
- Clear status display in red and green enables quick identification of trolley contents status
- Push bars allow ergonomic two-handed gripping for easy manoeuvring
- True-tracking mobility with swivel and fixed castors offers precise control and operational safety

EQUIPMENT FEATURES

- All-round bumper strip at the bottom**
The robust all-round bumper strip reliably protects against damage from collisions with trolleys or walls, ensuring your equipment stays intact and your workday safer.
- Closed design with hinged doors**
The closed design includes an all-round closed construction with hinged doors for easy handling. The design ensures safe storage and protects the inside of the transport trolley from external influences. The smooth surface is free of openings or crevices and facilitates cleaning. The robust stainless steel construction ensures both durability and high standards of hygiene.
- True-tracking mobility: 2 swivel castors, 2 fixed castors**
2 swivel castors, 2 fixed castors: The trolley stays on track, even under heavy loads. Precise manoeuvring, fewer corrections, greater operational safety.
- Stainless steel paper clip**
The robust stainless steel paper clip enables hygienic and secure attachment of trolley information. The corrosion-resistant material ensures a long service life even with intensive use.
- Transport latch incl. sealing**
The innovative locking system reliably protects the contents from unauthorised access and prevents accidental opening while driving. Thanks to the additional seal, it is possible to tell at any time whether the trolley has been opened without authorisation – a decisive advantage for sensitive areas.

- Clear status display**
The status display in red and green allows employees to quickly identify the status of the transported goods.
- Push bars**
Push bars are round tubes attached vertically to the corners of a transport trolley's body. Two-handed gripping at any handle height enables ergonomic, easy manoeuvring of the transport trolley.

Project _____

Order _____

Quantity _____

Date _____



GENERAL TECHNICAL DATA

Nominal format	StE baskets 600 × 300 mm
Quantity nominal format	6
Width actual	985 mm
Depth actual	751 mm
Height	1.471 mm
Weight	91 kg
Payload	120 kg
Main material	Stainless steel

INSERT PROPERTIES

Pitch	61,5 mm
--------------	---------

HOUSING PROPERTIES

Cart construction	Modular construction
Cart housing construction	Single-walled
Cover construction	Roof
Number of doors	2
Door construction	Double-walled Hinged doors
Door lock (closed)	Extension piece Transport latch with sealing tab
Door lock (open)	Extension piece
Max. Door opening angle	270 °
Door seal construction	Lip seal on door
With sealing flap	Yes

Sterile goods transport cart for 6 STU

INTERIOR PROPERTIES

Cart interior construction	Modular construction
Interior/compartment material	Stainless steel
Board construction	pitch_61_5 Insertable shelf
Number of shelves	2

MOBILITY

Set of castors	2 fixed castors 2 swivel castors with brakes
Castor attachment	Bolt-on panel
Chassis suitability	Off-premises transport
Castor bearing material	Stainless steel
Castor bearing type	Ball bearing
Castor housing material	Stainless steel
Wheel ø	160 mm
Type of tyre tread	Rubber – Standard
Antistatic wheels	No
Suitable for transport cart washing devices	Washing machine resistant
Towing device	Not available
HGV transport securing device	No
Impact protection construction	Bumper strip around the bottom
Push handle construction	Vertical push handle